



MODEL KAI-S NOTES

- TYPICALLY LOCATED 16" (406) OR 24" (610) ON CENTER
- ACCEPTS 1/4" (6) ANCHORS (BY OTHERS)
- REQUIRES MINIMUM 3/8" (10) DIA. HOLE THROUGH MODEL WALLMAT
- REQUIRES DRILLING 3/4" (19) DIA. HOLE THROUGH STUD TO SEAT NEOPRENE ELEMENT

DIMENSION FORMAT: IN [mm]



TITLE MODEL WALLMAT
STEEL-FRAMED INSTALLATION

LAST DATE
REVISED
4/24/14

DRAWN BY
MDV

DRAWING NO.
AA001811

AA